

GigaBit crimp contact - F, 0,08-0,12 mm²

GigaBit crimp contact - F, 0,08-0,12 mm²

Turned crimp contact

Female

Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)

Illustration



Product may differ from Image

Commercial data

ECLASS-6.0	27261204
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879672870
Packaging unit	100

Installation

Connection cross section min.	0,08 mm ²
Connection cross section max.	0,12 mm ²
AWG number min.	28
AWG number max.	26

Installation | Connection

Stripping length	4,2 mm
Connection	Crimp
Gender	female
Mating cycles min.	200

Mechanical data | Material data

Coating contact	gold plated
Material contact	Copper alloy

Mechanical data | Mounting data

Height	1,7 mm
Width	1,7 mm
Depth	13,6 mm