

Pneumatic insert - female, 6 mm

Pneumatic female

Internal hose Ø

6 mm

Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)

Illustration



Product may differ from Image

Commercial data

ECLASS-6.0	27261204
ECLASS-6.1	27261290
ECLASS-7.0	27440290
ECLASS-8.0	27440290
ECLASS-9.0	27440220
ECLASS-10.1	27440220
ECLASS-11.1	27440220
ECLASS-12.0	27440220
ETIM-5.0	EC000438
customs tariff number	39269097
GTIN	4048879672818
Packaging unit	10

Installation | Connection

Gender	female
Mating cycles min.	500

Mechanical data

Operating pressure max.	8 bar
Integrated valve	no

Mechanical data | Material data

Material housing	Delrin Acetal
------------------	---------------

Mechanical data | Mounting data

Internal hose Ø	6 mm
-----------------	------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	80 °C

