

Pneumatic insert with valve - female, 3 mm

Pneumatic female
Internal hose Ø
3 mm
Integrated valve
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

| Commercial data | |
|--|---------------|
| ECLASS-6.0 | 27261204 |
| ECLASS-6.1 | 27261290 |
| ECLASS-7.0 | 27440290 |
| ECLASS-8.0 | 27440290 |
| ECLASS-9.0 | 27440220 |
| ECLASS-10.1 | 27440220 |
| ECLASS-11.1 | 27440220 |
| ECLASS-12.0 | 27440220 |
| ETIM-5.0 | EC000438 |
| customs tariff number | 39269097 |
| GTIN | 4048879672832 |
| Packaging unit | 10 |
| Installation Connection | |
| Gender | female |
| Mating cycles min. | 500 |
| Mechanical data | |
| Operating pressure max. | 8 bar |
| Integrated valve | yes |
| Mechanical data Material data | |
| Material housing | Delrin Acetal |
| Mechanical data Mounting data | |
| Internal hose Ø | 3 mm |
| Environmental characteristics Climatic | |
| Operating temperature min. | -40 °C |

Operating temperature max. 80 °C