

MODL. VARIO 10-way coupling housing type B

nickel plated aluminum

Mobile housing (round)  
Aluminium  
10-way

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
customs tariff number	85389099
GTIN	4048879573061
Packaging unit	1
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed
Mechanical data	
Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar
Mechanical data   Material data	
Coating housing	powder-coated
Material housing	Aluminum die casting
Mechanical data   Mounting data	
Mounting method	screw fixing
Environmental characteristics   Climatic	

Operating temperature min.	-20 °C
Operating temperature max.	120 °C