

**MODL.VARIO Accessories closure plug 4/2**

for adaptive inserts, nickel plated brass

Modlink Vario

Accessories

Locking plug

Diameter

4 mm

Quantity: 10 pcs.

good resistance to oil, gasoline and chemicals

The resistance to aggressive media should be individually tested for your application. Further details on request.

**[Link to Product](#)****Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27260702
ECLASS-6.1	27269202
ECLASS-7.0	27449203
ECLASS-8.0	27449203
ECLASS-9.0	27440192
ECLASS-10.1	27440192
ECLASS-11.1	27440192
ECLASS-12.0	27440192
ETIM-5.0	EC002641
customs tariff number	85389099
GTIN	4048879618878
Packaging unit	10

**Mechanical data**

Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar

**Mechanical data | Material data**

Coating housing	nickel plated
Material housing	Brass

**Mechanical data | Mounting data**

Size	AD4
Height	19 mm

Width	5,5 mm
Depth	5,5 mm
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-20 °C
Operating temperature max.	120 °C