

MODL.VARIO Accessories closure plug 6/4

for adaptive inserts, nickel plated brass

Modlink Vario  
Accessories  
Locking plug  
Diameter  
6 mm  
Quantity: 10 pcs.  
good resistance to oil, gasoline and chemicals  
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

| Commercial data                 |               |
|---------------------------------|---------------|
| ECLASS-6.0                      | 27260702      |
| ECLASS-6.1                      | 27269202      |
| ECLASS-7.0                      | 27449203      |
| ECLASS-8.0                      | 27449203      |
| ECLASS-9.0                      | 27440192      |
| ECLASS-10.1                     | 27440192      |
| ECLASS-11.1                     | 27440192      |
| ECLASS-12.0                     | 27440192      |
| ETIM-5.0                        | EC002641      |
| customs tariff number           | 85389099      |
| GTIN                            | 4048879618885 |
| Packaging unit                  | 10            |
| Mechanical data                 |               |
| Operating pressure min.         | -0,8 bar      |
| Operating pressure max.         | 16 bar        |
| Mechanical data   Material data |               |
| Coating housing                 | nickel plated |
| Material housing                | Brass         |
| Mechanical data   Mounting data |               |
| Size                            | AD6           |
| Height                          | 19 mm         |

|   |        |
|---|--------|
| Width   | 8 mm   |
| Depth   | 8 mm   |
| <b>Environmental characteristics   Climatic</b> |        |
| Operating temperature min.                      | -20 °C |
| Operating temperature max.                      | 120 °C |