

**MODL. VARIO insert for fixed housing type B**

4/2 shut-off, stainless steel type 1.4404 (V4A)

Modlink Vario  
 Insert - stationary housing  
 Stainless steel 1.4404 (V4A)  
 with shut-off  
 AD4

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
customs tariff number	73269098
GTIN	4048879573887
Packaging unit	1

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed

**Mechanical data**

Barrier	with shut-off
Operating pressure min.	0 bar
Operating pressure max.	16 bar

**Mechanical data | Material data**

Material gasket	FPM
Material housing	Stainless steel 1.4404 (V4A)

**Mechanical data | Mounting data**

The information in this Product-PDF has been compiled with the utmost care.  
 Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-05-02

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Outer diameter hose	4 mm
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-20 °C
Operating temperature max.	120 °C