

**MODL. VARIO insert for fixed housing type B**

4/2 shut-off, dezincification resistant brass

Modlink Vario  
Insert - stationary housing  
Brass, dezincification-resistant  
with shut-off  
AD4

[Link to Product](#)

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
customs tariff number	74198090
GTIN	4048879574259
Packaging unit	1
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed
Mechanical data	
Barrier	with shut-off
Operating pressure min.	0 bar
Operating pressure max.	16 bar
Mechanical data   Material data	
Material gasket	FPM
Material housing	Brass
Mechanical data   Mounting data	

Outer diameter hose	4 mm
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-20 °C
Operating temperature max.	120 °C