


**MODL. VARIO insert for coupling housing type B**

8/6 no shut-off, stainless steel type 1.4404 (V4A)

Modlink Vario  
 Stainless steel 1.4404 (V4A)  
 without shut-off  
 AD8

**[Link to Product](#)****Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
customs tariff number	73269098
GTIN	4048879572507
Packaging unit	1

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed

**Mechanical data**

Barrier	without shut-off
Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar

**Mechanical data | Material data**

Material gasket	FPM
Material housing	Stainless steel 1.4404 (V4A)

**Mechanical data | Mounting data**

Outer diameter hose 8 mm

Environmental characteristics   Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	120 °C