

**MODL. VARIO insert for fixed housing type B**

6/4 non-drip, dezincification resistant brass

Insert - stationary housing  
 Brass, dezincification-resistant  
 drip-free  
 AD6

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27260702      |
| ECLASS-6.1            | 27260708      |
| ECLASS-7.0            | 27440312      |
| ECLASS-8.0            | 27440312      |
| ECLASS-9.0            | 27440312      |
| ECLASS-10.1           | 27440312      |
| ECLASS-11.1           | 27440312      |
| ECLASS-12.0           | 27440312      |
| ETIM-5.0              | EC002641      |
| customs tariff number | 74198090      |
| GTIN                  | 4048879572927 |
| Packaging unit        | 1             |

**Device protection | Electrical**

|  |                   |
|--|-------------------|
| Degree of protection (EN IEC 60529)    | IP65, IP67, IP68  |
| Degree of protection (ISO 20653:2013)  | IP66K, IP69K      |
| Additional condition protection degree | inserted, screwed |

**Mechanical data**

|                         |           |
|-------------------------|-----------|
| Barrier                 | drip-free |
| Operating pressure min. | 0 bar     |
| Operating pressure max. | 16 bar    |

**Mechanical data | Material data**

|                  |       |
|------------------|-------|
| Material gasket  | FPM   |
| Material housing | Brass |

**Mechanical data | Mounting data**

### Environmental characteristics | Climatic

|                            |        |
|----------------------------|--------|
| Operating temperature max. | 120 °C |
|----------------------------|--------|