

**MODL. VARIO insert for fixed housing type B**

8/6 non-drip, dezincification resistant brass

Insert - stationary housing  
 Brass, dezincification-resistant  
 drip-free  
 AD8

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
customs tariff number	74198090
GTIN	4048879572941
Packaging unit	1

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed

**Mechanical data**

Barrier	drip-free
Operating pressure min.	0 bar
Operating pressure max.	16 bar

**Mechanical data | Material data**

Material gasket	FPM
Material housing	Brass

**Mechanical data | Mounting data**

### Environmental characteristics | Climatic

Operating temperature max.	120 °C
----------------------------	--------