MURR ELEKTRONIK
stay connected


## MASI20 INSTALLATION TECHNOLOGY


Distributor AS-I and extern power, 1 potential


5 ports, universal
1 potential
5 plug terminals included

[Link to Product]

### Illustration






Product may differ from Image

### Commercial data

| | |
|---|---|
| ECLASS-6.0 | 27279219 |
| ECLASS-6.1 | 27279219 |
| ECLASS-7.0 | 27279219 |
| ECLASS-8.0 | 27279219 |
| ECLASS-9.0 | 27440108 |
| ECLASS-10.1 | 27440111 |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

MURR ELEKTRONIK
stay connected

| | |
|---|---|
| ECLASS-11.1 | 27440111 |
| ECLASS-12.0 | 27440111 |
| ETIM-5.0 | EC001596 |
| customs tariff number | 85369010 |
| GTIN | 4048879050463 |
| Packaging unit | 1 |
| **Electrical data \| Supply** | |
| Operating voltage DC max. | 36 V |
| Current operating per port max. | 8 A |
| Total current max. | 12 A |
| **Device protection \| Electrical** | |
| Degree of protection (EN IEC 60529) | IP20 |
| Insulation strength Power/Power (EN 60664-1) | 50 V |
| Insulation strength ASI/Power | 200 V |
| **Mechanical data \| Mounting data** | |
| Mounting method | geschnappt |
| Suitable for mounting type | mounting rail, (EN 60715) |
| Height | 61 mm |
| Width | 25 mm |
| Depth | 152 mm |
| **Environmental characteristics \| Climatic** | |
| Operating temperature min. | -20 °C |
| Operating temperature max. | 70 °C |
| **Conformity** | |
| Product standard | EN 60664-1 |
| **Connection type 6** | |
| Connection type 1 | 11 |
| Connection type 2 | 12 |
| Connection type 3 | 13 |
| Connection type 4 | 14 |
| Connection type 5 | 15 |
| Connection type 6 | Power / Asi |
| Connection | Screw terminals SK |
| Family construction form | terminal |
| Gender | female |
| Color contact carrier | green |
| No. of poles | 2 |
| PIN 1 | 11 + |
| PIN 2 | 11 - |
| Connection | Screw terminals SK |
| Family construction form | terminal |
| Gender | female |
| Color contact carrier | green |
| No. of poles | 2 |
| PIN 1 | 12 + |
| PIN 2 | 12 - |
| Connection | Screw terminals SK |
| Family construction form | terminal |
| Gender | female |
| Color contact carrier | green |
| No. of poles | 2 |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

| | |
|---|---|
| PIN 1 | 13 + |
| PIN 2 | 13 - |
| Connection | Screw terminals SK |
| Family construction form | terminal |
| Gender | female |
| Color contact carrier | green |
| No. of poles | 2 |
| PIN 1 | 14 + |
| PIN 2 | 14 - |
| Connection | Screw terminals SK |
| Family construction form | terminal |
| Gender | female |
| Color contact carrier | green |
| No. of poles | 2 |
| PIN 1 | 15 + |
| PIN 2 | 15 - |
| Connection | Screw terminals SK |
| Family construction form | terminal |
| Gender | female |
| Color contact carrier | green |
| No. of poles | 4 |
| PIN 1 | 1 + |
| PIN 2 | 1 - |
| PIN 3 | 2 + |
| PIN 4 | 2 - |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28