MURR ELEKTRONIK
stay connected

S-Lamp 30 S L M12(4)


Lamp

S-Lamp 30 S L M12(4)
Lamp
Frontring stainless steel
Mounting hole 30,3 mm
Connection M12 (4-pin)

Link to Product

Illustration





Product may differ from Image

Commercial data

ECLASS-6.1	27371223
ECLASS-7.0	27371223
ECLASS-8.0	27371223
ECLASS-9.0	27371223
ECLASS-10.1	27371223
ECLASS-11.1	27371223
ECLASS-12.0	27371223
customs tariff number	94054231
GTIN	4065909019641
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	20 V
Operating voltage DC max.	28 V
Rated operating current	0,01 A
Operating current max.	12 mA

Electrical data | Input

Short-circuit current	1000 A

Installation | Connection

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

MURR ELEKTRONIK
stay connected

Family construction form	M12
Installation | Pin assignment	
Coding	A
No. of poles	4
Device protection | Electrical	
Installation height max. ASL	2000 m
Degree of protection front (EN IEC 60529)	IP66, IP67, IP69
Degree of protection back (EN IEC 60529)	IP66, IP67
Pollution Degree	2
Rated insulation voltage	250 V
Short circuit protective device (SCPD)	fuse 250 V / 0.1 A / 1.5 kA gG quick
Overvoltage category (EN 60950-1)	II
Device protection | Mechanical	
UL enclosure type rating front side	type 4X
Device protection | Media	
Salt-spray resistance (IEC 60068-2-11)	yes
Mechanical data	
Can be illuminated	yes
Color	black
Color collar	black
Color front ring	Stainless steel
Color illuminant	white
Shape collar	round
Type of illuminant	LED
Mechanical data | Material data	
Material housing	Plastic
Mechanical data | Mounting data	
Mounting method	Threaded ring
Installation height	3,9 mm
Mounting depth	36,4 mm
Mounting hole	30,3 mm
Height	34,5 mm
Width	40 mm
Grid min.	35 mm
Environmental characteristics | Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Derating from	40 °C
Storage temperature min.	-40 °C
Storage temperature max.	90 °C
Relative humidity max. (operation)	93 %
Connection type 2	
Family construction form	M12
Gender	male
Color contact carrier	black
Coding	A
No. of poles	4
PIN 2	LED (A)
PIN 3	LED (K)
Family construction form	M12

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

Gender	male
Coding	A
No. of poles	4
PIN 2	LED (A)
PIN 3	LED (K)

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28