MURR ELEKTRONIK
stay connected

1,6 mm crimp contact f/turned/silver/1,5 mm²

100 pieces

Turned crimp contact
Female
1.6 mm
1.5 mm² (AWG 16)
Quantity: 100 pcs.
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879653541
Packaging unit	100
Installation	
Connection cross section max.	1,5 mm²
AWG number max.	16
Installation | Connection	
Stripping length	7 mm
Connection	Crimp
Gender	female
Mating cycles min.	500
Mechanical data | Material data	
Coating contact	silver-plated

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

Material contact	Brass

Mechanical data | Mounting data	
Height	3,5 mm
Width	3,5 mm
Depth	21,6 mm

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28