MURR ELEKTRONIK
stay connected

Reset button with 1 illuminated push button


1 NO contact in a IP65 enclosure


R-Button / 42 1NO L M12(4)
with M12 connection
4-pole
1 button can be lit (1 NO contact)
Delivery contents:
Flat lens, transparent clear, red, yellow, green, blue
Label plates, O, I, R
mounting with clip on the back side


Link to Product

Illustration









Product may differ from Image

Commercial data

ECLASS-6.0	27371228
ECLASS-6.1	27371228

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

MURR ELEKTRONIK
stay connected

ECLASS-7.0	27371228
ECLASS-8.0	27371228
ECLASS-9.0	27371228
ECLASS-10.1	27371228
ECLASS-11.1	27371228
ECLASS-12.0	27371228
ETIM-5.0	EC000225
customs tariff number	85365080
GTIN	4048879600507
Packaging unit	1
Electrical data	
Operating voltage AC/DC LED illumination max.	30 V
Operating current LED illumination	14 mA @24 V DC
Electrical data | Output	
Utilization category AC-15 (EN IEC 60947-5-1)	1,5 A @ 240 V
Utilization category DC-13 (EN IEC 60947-5-1)	2 A @ 24 V
Switching current (AC-15)	15 A
Switching current (DC-13)	2,2 A
Device protection	
Condition lifetime	load-dependent, temperature dependent
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP65
Electrical lifetime	1000000 Cycles
Device protection | Mechanical	
Mechanical endurance	1000000 Cycles
Operating life B10d	1000000 Cycles
Mechanical data	
Bounce time max.	10 ms
Mechanical data | Material data	
Material contact	AgNi
Mechanical data | Mounting data	
Height	29 mm
Width	124 mm
Depth	42 mm
Environmental characteristics | Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C
Technical Data | Reliability	
Lambda normally open contact	50 %
Connection type 1	
Family construction form	M12
Gender	male
Color contact carrier	black
Coding	A
No. of poles	4
PIN 1	NO
PIN 2	X 1 +

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

PIN 3	X 2 -
PIN 4	NO

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29