MURR ELEKTRONIK
stay connected

AIDA PUSH PULL COUPLING HAN24

with power (5 pole) spring clamp + RJ45 fem/fem


with RJ45 and energy
1× RJ45, 8-pole metal, CAT5e (female/female)
Combicon Power/spring clamp terminal, Push Pull
Size 24

Link to Product

Illustration



Product may differ from Image



Size		6	24
Wall cut-out	L1	52	112
	L2	35	35
Distance of holes	L3	70	130
	L4	32	32

Commercial data

ECLASS-6.0	27143423
ECLASS-6.1	27143423
ECLASS-7.0	27449001
ECLASS-8.0	27449001
ECLASS-9.0	27440321
ECLASS-10.1	27440321
ECLASS-11.1	27440321
ECLASS-12.0	27440321
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879031165
Packaging unit	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65

Mechanical data | Material data

Material housing	PA

Mechanical data | Mounting data

Height	146 mm
Width	58 mm
Depth	65 mm

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29

Environmental characteristics | Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	70 °C

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-29