

**EXACT12, 8XM12, 4 POLE**

Conn.M12 12-pole

Art.No.: 8000-88460-0000000

Weight: 0.150 kg

Country of origin: DE

Model designation: MVP12N-GS8V

8-way




4-pole (port 3...8)


5-pole (port 1+2)

M12 plug connection, 12-pole

with LED for digital PNP-signals 24 V DC

Plastic housings with good resistance against chemicals and oils.

[Link to Product](#)
**Illustration**




Product may differ from Image



#### Header

Material short text MVP12N-GS8V

#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/8000-88460-0000000">https://shop.murrelektronik.com/8000-88460-0000000</a>
GTIN	4048879313155
ECLASS-6.0	27143423
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879313155
Packaging unit	1

#### Electrical data | Supply

Operating voltage DC	24 V
Current operating per contact max.	1,5 A
Total current max.	1,5 A

#### Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67, IP65
-------------------------------------	------------

**Device protection | Media**

Flame resistance	flame retardant
------------------	-----------------

**Mechanical data | Material data**

Material housing	Plastic
------------------	---------

**Environmental characteristics | Climatic**

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	70 °C
----------------------------	-------

**Connection type 2**

Family construction form	M12
--------------------------	-----

No. of poles	4
--------------	---

Coding	A
--------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

PIN 1	+
-------	---

PIN 2	n.c.
-------	------

PIN 3	-
-------	---

PIN 4	NO S 1
-------	--------

PIN 5	PE
-------	----

Family construction form	M12
--------------------------	-----

No. of poles	12
--------------	----

Coding	A
--------	---

Gender	male
--------	------

Color contact carrier	black
-----------------------	-------

PIN 1	+
-------	---

PIN 2	-
-------	---