

MODLINK MSDD DATA INSERT

1×SUB-D9 male/male + 1×RJ45 + 2×PS2 fem./soldering

RJ45; SUB-D9; PS2; PS2
1 × RJ45, 8-pole metal, CAT5e (female/female)
1 × SUB-D9 (male/male)
2× PS2 (6-pole solder connection)

Link to Product

Illustration



Product may differ from Image



Commercial data

| | |
|-----------------------|---------------|
| ECLASS-6.0 | 27189217 |
| ECLASS-6.1 | 27189217 |
| ECLASS-7.0 | 27189217 |
| ECLASS-8.0 | 27189217 |
| ECLASS-9.0 | 27182806 |
| ECLASS-10.1 | 27182806 |
| ECLASS-11.1 | 27182806 |
| ECLASS-12.0 | 27182806 |
| ETIM-5.0 | EC002625 |
| customs tariff number | 85366990 |
| GTIN | 4048879037464 |
| Packaging unit | 1 |

Mechanical data | Mounting data

| | |
|--------|-------|
| Height | 88 mm |
| Width | 51 mm |
| Depth | 21 mm |

Environmental characteristics | Climatic

| | |
|--------------------------|-------|
| Storage temperature min. | 5 °C |
| Storage temperature max. | 40 °C |

SUB-D9

| | |
|---------------------------------------|--|
| Operating voltage AC | 48 V |
| Operating voltage DC | 48 V |
| Operating voltage AC max. (UL-listed) | 30 V |
| Operating voltage DC max. (UL-listed) | 42,4 V |
| Operating current | 3 A |
| Current operating max. (UL) | 175 mA |
| Family construction form | SUB-D9 |
| Family type Back side | SUB-D9 |
| Gender | male |
| Gender Rear | male |
| Looking techniques | Standard UNC 4-40 screw thread bolt (EN 60807) |
| No. of poles | 9 |

RJ45

| | |
|---------------------------------------|-------------------|
| Operating voltage AC max. (UL-listed) | 30 V |
| Operating voltage DC max. (UL-listed) | 42,4 V |
| Current operating max. (UL) | 175 mA |
| Family construction form | RJ45 |
| Family type Back side | RJ45 |
| Cable category min. | Cat5e |
| Looking techniques | Snap-in connector |

PS2

| | |
|-------------------------------|---------------------|
| Connection cross section max. | 0,5 mm ² |
| AWG number max. | 20 |
| Operating voltage AC | 30 V |
| Operating voltage DC | 30 V |
| Operating current | 1 A |
| Family construction form | PS2 |
| Family type Back side | PS2 |
| Gender | female |
| Gender Rear | Lötanschluss |
| Looking techniques | Screw locking |
| No. of poles | 6 |