

**MIRO 6.2 110V-1U OUTPUT RELAY**

IN: 110 VAC/DC - OUT: 250 VAC/DC / 6 A

Art.No.: 52030

Weight: 0.035 kg

Country of origin: CZ




Model designation: MIRO 6,2-1AUSG.REL.110V-1U


1 NO/NC contact

6 A

110 V AC/DC

Screw terminals

[Link to Product](#)**Illustration**



Product may differ from Image



#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/52030">https://shop.murrelektronik.com/52030</a>
GTIN	4048879027199
Customs tariff number	85364900
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879027199
Packaging unit	1

#### Electrical data | Input

Input voltage AC	110 V
Input voltage AC min.	95 V
Input voltage AC max.	121 V
Input voltage DC	110 V
Input voltage DC min.	95 V
Input voltage DC max.	121 V
Input current	4 mA

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-05-05

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

<b>Electrical data   Output</b>	
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current max.	6 A
Switching current DC	10 mA
Power rating AC max.	1.500 VA
Power rating DC max.	120 W
Utilization category AC-12 (EN IEC 60947-5-1)	6 A @ 24 V 6 A @ 110 V 6 A @ 230 V
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V 3 A @ 110 V 3 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1 A @ 24 V 0.2 A @ 110 V 0.1 A @ 230 V
<b>Diagnostics</b>	
Status indication LED	green
<b>Device protection</b>	
Condition lifetime	load-dependent
<b>Device protection   Electrical</b>	
Electrical lifetime	0 cycles
<b>Device protection   Mechanical</b>	
Mechanical endurance	0 cycles
<b>Mechanical data</b>	
Response time max.	10 ms
Drop-out time max.	15 ms
Bounce time max.	1,5 ms
<b>Mechanical data   Material data</b>	
Material contact	Ag Sn O2
<b>Mechanical data   Mounting data</b>	
Height	91 mm
Width	6,2 mm
Depth	71 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-20 °C
Operating temperature max.	55 °C
<b>Connection type 5</b>	
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	12
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	11
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green

Connection	Screw terminals SK
PIN 1	14
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	A 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	A 2