

**MIRO 6.2 24VDC-1S OUTPUT RELAY**

IN: 24 VDC - OUT: 250 VAC/DC / 6 A

Art.No.: 52002

Weight: 0.030 kg

Country of origin: CZ

Model designation: MIRO 6,2-1AUSG.REL.24VDC-1S




1 NO contact


6 A

24 V DC

Screw terminals

safe separation (EN 60947-1)

[Link to Product](#)**Illustration**



Product may differ from Image

**Commercial data**

URL Webshop	<a href="https://shop.murrelektronik.com/52002">https://shop.murrelektronik.com/52002</a>
GTIN	4048879027298
Customs tariff number	85364900
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879027298
Packaging unit	1

**Electrical data | Input**

Input voltage DC	24 V
Input voltage DC min.	19,2 V
Input voltage DC max.	30 V
Input current	14 mA

**Electrical data | Output**

Switching voltage AC max.	250 V
---------------------------	-------

Switching voltage DC max.	250 V
Switching current max.	6 A
Switching current DC	100 mA
Switching frequency max.	10 Hz
Power rating AC max.	1.500 VA
Power rating DC max.	120 W
Utilization category AC-12 (EN IEC 60947-5-1)	6 A @ 24 V 6 A @ 110 V 6 A @ 230 V
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V 3 A @ 110 V 3 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1 A @ 24 V 0.2 A @ 110 V 0.1 A @ 230 V

#### Diagnostics

Status indication LED	green
-----------------------	-------

#### Device protection

Condition lifetime	load-dependent
--------------------	----------------

#### Device protection | Electrical

Electrical lifetime	0 cycles
Rated surge voltage	4 kV

#### Device protection | Mechanical

Mechanical endurance	0 cycles
----------------------	----------

#### Mechanical data

Response time max.	10 ms
Drop-out time max.	15 ms
Bounce time max.	1,5 ms

#### Mechanical data | Material data

Material contact	Ag Sn O <sub>2</sub>
------------------	----------------------

#### Mechanical data | Mounting data

Height	78 mm
Width	6,2 mm
Depth	70 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail

#### Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	60 °C

#### Connection type 4

Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	13
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	14
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green

Connection	Screw terminals SK
PIN 1	A 1 +
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	A 2 -