

### MIRO MULTI TIMER 24VDC-1S



MIRO 6.2 MULTI-TIMER 24VDC-1S

Art.No.: 52350  
 Weight: 0.036 kg  
 Country of origin: CZ  
 Model designation: MIRO MULTI TIMER 24VDC-1S



Relay output  
 Impulse expansion: 0.1...300 s  
 Screw terminals  
 safe separation (EN 60947-1)

[Link to Product](#)

**Illustration**



Time	+A1	Function
0.1...1.2 s	Out	Switch on delay
0.4...5 s	Out	One shot
3.5...40 s	Out	Modulation, pause starting
30...300 s	Load	Modulation, pulse starting
	B1	Switch off delay time



Product may differ from Image

**Commercial data**

URL Webshop	<a href="https://shop.murrelektronik.com/52350">https://shop.murrelektronik.com/52350</a>
GTIN	4048879026956
Customs tariff number	85364190
ECLASS-6.0	27210990
ECLASS-6.1	27371790
ECLASS-7.0	27371790
ECLASS-7.1	27371790
ECLASS-8.0	27371605
ECLASS-8.1	27371605
ECLASS-9.0	27371605
ECLASS-9.1	27371605
ECLASS-10.0.1	27371605
ECLASS-10.1	27371605
ECLASS-11.0	27371605
ECLASS-11.1	27371605
ECLASS-12.0	27371605
ECLASS-13.0	27371605
ECLASS-14.0	27371605
ETIM-5.0	EC001439
ETIM-6.0	EC001439
ETIM-7.0	EC001439
ETIM-8.0	EC001439
customs tariff number	85364190
EAN	4048879026956
Packaging unit	1

**Electrical data | Input**

Input voltage DC	24 V
Input voltage DC min.	20,4 V
Input voltage DC max.	26,4 V
Input current	20 mA
Input current DC max.	16 mA
Control voltage DC	24 V
Control voltage DC min.	20,4 V

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-05-05

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Control voltage DC max.	26,4 V
Control current	5 mA
<b>Electrical data   Output</b>	
Output voltage adjustable	No
Output current max.	6 A
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current DC	100 mA
Switching frequency max.	10 Hz
Power rating AC max.	1.500 VA
Power rating DC max.	120 W
<b>Device protection</b>	
Condition lifetime	load-dependent
<b>Device protection   Electrical</b>	
Electrical lifetime	0 cycles
Rated surge voltage	4 kV
<b>Device protection   Mechanical</b>	
Mechanical endurance	0 cycles
<b>Mechanical data</b>	
Response time max.	10 ms
Drop-out time max.	15 ms
Bounce time max.	1,5 ms
<b>Mechanical data   Material data</b>	
Material contact	Ag Sn O <sub>2</sub>
<b>Mechanical data   Mounting data</b>	
Height	91 mm
Width	6,2 mm
Depth	71 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-25 °C
Operating temperature max.	60 °C
<b>Connection type 5</b>	
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	+ A 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	18
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green

Connection	Screw terminals SK
PIN 1	17
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	+ B 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	- A 2