

MIRO MULTI TIMER 24VDC-1S

MIRO 6.2 MULTI-TIMER 24VDC-1S

Art.No.: 52350 Weight: 0.036 Country of origin: CZ

Model designation: MIRO MULTI TIMER 24VDC-1S

Relay output

Impulse expansion: 0.1...300 s


Screw terminals


safe separation (EN 60947-1)


Link to Product

Illustration













stay connected





Product may differ from Image



Header







Material short text	MIRO MULTI TIMER 24VDC-1S
Commercial data	
URL Webshop	https://shop.murrelektronik.com/52350
GTIN	4048879026956
ECLASS-6.0	27210990
ECLASS-6.1	27371790
ECLASS-7.0	27371790
ECLASS-7.1	27371790
ECLASS-8.0	27371605
ECLASS-8.1	27371605
ECLASS-9.0	27371605
ECLASS-9.1	27371605
ECLASS-10.0.1	27371605
ECLASS-10.1	27371605
ECLASS-11.0	27371605
ECLASS-11.1	27371605
ECLASS-12.0	27371605
ECLASS-13.0	27371605
ECLASS-14.0	27371605
ETIM-5.0	EC001439
ETIM-6.0	EC001439
ETIM-7.0	EC001439
ETIM-8.0	EC001439
customs tariff number	85364190
EAN	4048879026956
Packaging unit	1
Electrical data Input	
Input voltage DC	24 V
Input voltage DC min.	20.4 V
Input voltage DC max.	26.4 V
Input current	20 mA
Input current DC max.	16 mA

The information in this Product-PDF has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-11-03



stay connected

Control voltage DC	24 V
Control voltage DC min.	20.4 V
Control voltage DC max.	26.4 V
Control current	5 mA
Electrical data Output	
Output voltage adjustable	no
Output current max.	6 A
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current DC	100 mA
Switching frequency max.	10 Hz
Power rating AC max.	1,500 VA
Power rating DC max.	120 W
Device protection	
Condition lifetime	load-dependent
Device protection Electrical	
Electrical lifetime	0 cycles
Rated surge voltage	4 kV
	• • •
Device protection Mechanical	
Mechanical endurance	0 cycles
Mechanical data	
Response time max.	10 ms
Drop-out time max.	15 ms
Bounce time max.	1.5 ms
Mechanical data Material data	
Material contact	Ag Sn O2
Mechanical data Mounting data	
Height	91 mm
Width	6.2 mm
Depth	71 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail
Environmental characteristics Climatic	(a. c.
	05.00
Operating temperature min.	-25 °C
Operating temperature max.	60 °C
Connection type 5	
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	+ A 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	18
Family construction form	terminal
No. of poles	1
Gender	female

The information in this Product-PDF has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-11-03



Color contact carrier	green
Connection	Screw terminals SK
PIN 1	17
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	+ B 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	- A 2