

**MIRO MULTI TIMER 24VDC-1S**



MIRO 6.2 MULTI-TIMER 24VDC-1S

Art.No.: 52350  
Weight: 0.036  
Country of origin: CZ  
Model designation: MIRO MULTI TIMER 24VDC-1S

Relay output  
Impulse expansion: 0.1...300 s  
Screw terminals  
safe separation (EN 60947-1)

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27210990
ECLASS-6.1	27371790
ECLASS-7.0	27371790

ECLASS-8.0	27371605
ECLASS-9.0	27371605
ECLASS-10.1	27371605
ECLASS-11.1	27371605
ECLASS-12.0	27371605
ETIM-5.0	EC001439
customs tariff number	85364190
customs tariff number	85364190
EAN	4048879026956
EAN	4048879026956
Packaging unit	1
Packaging unit	1

#### Electrical data | Input

Input voltage DC	24 V
Input voltage DC min.	20,4 V
Input voltage DC max.	26,4 V
Input current	20 mA
Input current DC max.	16 mA
Control voltage DC	24 V
Control voltage DC min.	20,4 V
Control voltage DC max.	26,4 V
Control current	5 mA

#### Electrical data | Output

Output voltage adjustable	no
Output current max.	6 A
Switching frequency max.	10 Hz
Power rating AC max.	1500 VA
Power rating DC max.	120 W
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current DC	100 mA

#### Device protection

Condition lifetime	load-dependent
--------------------	----------------

#### Device protection | Electrical

Rated surge voltage	4 kV
Electrical lifetime	20000000 Cycles

#### Device protection | Mechanical

Mechanical endurance	20000000 Cycles
----------------------	-----------------

#### Mechanical data

Drop-out time max.	15 ms
Response time max.	10 ms
Bounce time max.	1,5 ms

#### Mechanical data | Material data

Material contact	Ag Sn O2
------------------	----------

#### Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	91 mm
Width	6,2 mm
Depth	71 mm

#### Environmental characteristics | Climatic

Operating temperature min.	-25 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

#### Connection type 5

Connection	Screw terminals SK
------------	--------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

No. of poles	1
--------------	---

PIN 1	+ A 1
-------	-------

Connection	Screw terminals SK
------------	--------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

No. of poles	1
--------------	---

PIN 1	18
-------	----

Connection	Screw terminals SK
------------	--------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

No. of poles	1
--------------	---

PIN 1	17
-------	----

Connection	Screw terminals SK
------------	--------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

No. of poles	1
--------------	---

PIN 1	+ B 1
-------	-------

Connection	Screw terminals SK
------------	--------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

No. of poles	1
--------------	---

PIN 1	- A 2
-------	-------