

IMPACT67 COMPACT MODULE, PLASTIC

Ethercat, 16 dig Out

Art.No.: 55084
Weight: 0.44
Country of origin: DE
Model designation: IMPACT67 EC DO 16/0,5A


Digital outputs
DO16 - 0.5 A
Ethernet 10/100 Mbit/s; M12, D-coded
7/8", 5-pole, 2× max. 9 A
M12, 5-pole, A-coded
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.
mounting compatible with I/O modules of the MVK series

Link to Product

Illustration



Product may differ from Image



| Commercial data | |
|-----------------------|---------------|
| ECLASS-6.0 | 27242604 |
| ECLASS-6.1 | 27242604 |
| ECLASS-7.0 | 27242604 |
| ECLASS-8.0 | 27242604 |
| ECLASS-9.0 | 27242604 |
| ECLASS-10.1 | 27242604 |
| ECLASS-11.1 | 27242604 |
| ECLASS-12.0 | 27242604 |
| ETIM-5.0 | EC001599 |
| customs tariff number | 85389099 |
| customs tariff number | 85389099 |
| GTIN | 4048879051965 |
| GTIN | 4048879051965 |
| Packaging unit | 1 |

Packaging unit 1

Electrical data | Supply

Total current UA max. 9 A
Total current US max. 9 A

Electrical data | Output

Overload resistant yes
Short-circuit protected yes
Output current per pin max. 0,5 A

Industrial communication | Bus data

Address setting type Rotary switch, automatic

Diagnostics

Diagnostic No voltage, Under voltage
Diagnostic via BUS per module and channel
Diagnostic via LED per module and channel
LED display Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529) IP67

Mechanical data | Mounting data

Suitable for mounting type 2-hole screw mounting
Height 39 mm
Width 63 mm
Depth 225 mm

Environmental characteristics | Climatic

Operating temperature min. 0 °C
Operating temperature max. 55 °C
Storage temperature min. -25 °C
Storage temperature max. 70 °C

Connection type 4

Connection type 1 0-7
Connection type 2 Port1, Port2
Connection type 3 Power In
Connection type 4 Power Out
Family construction form M12
Gender female
Color contact carrier black
Coding A
No. of poles 5
PIN 1 n.c.
PIN 2 DO 10-17
PIN 3 0 V
PIN 4 DO 00-07
PIN 5 PE
Mounting method inserted, screwed
Tightening torque 0,6 Nm
Family construction form M12
Gender female
Color contact carrier black
Coding D
No. of poles 4
PIN 1 TD +
PIN 2 RD +

| | |
|--------------------------|--------------|
| PIN 3 | TD - |
| PIN 4 | RD - |
| Family construction form | 7/8" |
| Gender | male |
| Color contact carrier | black |
| No. of poles | 5 |
| PIN 1 | 0 V |
| PIN 2 | 0 V |
| PIN 3 | PE |
| PIN 4 | 24 V DC (US) |
| PIN 5 | 24 V DC (UA) |
| Family construction form | 7/8" |
| Gender | female |
| Color contact carrier | black |
| No. of poles | 5 |
| PIN 1 | 0 V |
| PIN 2 | 0 V |
| PIN 3 | PE |
| PIN 4 | 24 V DC (US) |
| PIN 5 | 24 V DC (UA) |