

IMPACT67 COMPACT MODULE, PLASTIC

Ethernet/IP, 16 dig Out

Art.No.: 55088  
Weight: 0.44  
Country of origin: DE  
Model designation: IMPACT67 E DO 16/0,5A


Digital outputs  
DO16 - 0.5 A  
Ethernet 10/100 Mbit/s; M12, D-coded  
7/8", 5-pole, 2× max. 9 A  
M12, 5-pole, A-coded  
Connection cables are in the online shop under "Connection Technology".  
Housing fully potted.  
mounting compatible with I/O modules of the MVK series

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ETIM-5.0	EC001599
customs tariff number	85389099
customs tariff number	85389099
GTIN	4048879051927
GTIN	4048879051927
Packaging unit	1

Packaging unit 1

#### Electrical data | Supply

Total current UA max. 9 A  
Total current US max. 9 A

#### Electrical data | Output

Overload resistant yes  
Short-circuit protected yes  
Output current per pin max. 0,5 A

#### Industrial communication | Ethernet/IP

EtherNet/IP addressing BOOTP, DHCP, Rotary switch

#### Diagnostics

Diagnostic No voltage, Under voltage  
Diagnostic via BUS per module and channel  
Diagnostic via LED per module and channel  
LED display Ethernet connection/data traffic

#### Device protection | Electrical

Degree of protection (EN IEC 60529) IP67

#### Mechanical data | Mounting data

Suitable for mounting type 2-hole screw mounting  
Height 39 mm  
Width 63 mm  
Depth 225 mm

#### Environmental characteristics | Climatic

Operating temperature min. 0 °C  
Operating temperature max. 55 °C  
Storage temperature min. -25 °C  
Storage temperature max. 70 °C

#### Connection type 4

Connection type 1 0-7  
Connection type 2 Port1, Port2  
Connection type 3 Power In  
Connection type 4 Power Out  
Family construction form M12  
Gender female  
Color contact carrier black  
Coding A  
No. of poles 5  
PIN 1 n.c.  
PIN 2 DO 10-17  
PIN 3 0 V  
PIN 4 DO 00-07  
PIN 5 PE  
Mounting method inserted, screwed  
Tightening torque 0,6 Nm  
Family construction form M12  
Gender female  
Color contact carrier black  
Coding D  
No. of poles 4  
PIN 1 TD +  
PIN 2 RD +

PIN 3	TD -
PIN 4	RD -
Family construction form	7/8"
Gender	male
Color contact carrier	black
No. of poles	5
PIN 1	0 V
PIN 2	0 V
PIN 3	PE
PIN 4	24 V DC (US)
PIN 5	24 V DC (UA)
Family construction form	7/8"
Gender	female
Color contact carrier	black
No. of poles	5
PIN 1	0 V
PIN 2	0 V
PIN 3	PE
PIN 4	24 V DC (US)
PIN 5	24 V DC (UA)