

IMPACT67 PN DI16 M12L 4P galvanic separation

PROFINET, compact module

Art.No.: 55153

Weight: 0.486

Country of origin: DE

Model designation: IMPACT67 PN DI16 M12L 4P

Digital inputs

M12 power, 4-pin, L-coded, 2× max. 12 A

DI16 (IRT)

Ethernet 10/100 Mbit/s; M12, D-coded

M12, 5-pole, A-coded

FSU (Fast-Start-Up)


Galvanic isolation

Connection cables are in the online shop under "Connection Technology".

Housing fully potted.

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
customs tariff number	85389099
GTIN	4048879852234
Packaging unit	1

Electrical data | Supply

Norm operating voltage	EN 61131-2
Operating voltage US DC	24 V

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-05-13

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Total current UA max.	12 A
-----------------------	------

Total current US max.	12 A
-----------------------	------

Electrical data | Input

Type input	PNP, for 3-wire sensors or mechanical switches
------------	--

Overload resistant	yes
--------------------	-----

Short-circuit protected	yes
-------------------------	-----

Sensor current US per input max.	0,2 A
----------------------------------	-------

Industrial communication

Supported protocol	PROFINET
--------------------	----------

Industrial communication | Profinet

Number of active connections (IO controller) max.	2
---	---

FSU (Fast-Start-Up)	yes
---------------------	-----

Fast start up time max.	0,5 s
-------------------------	-------

IRT (network communication)	yes
-----------------------------	-----

PROFINET Netload Class	III
------------------------	-----

PROFINET addressing	DCP
---------------------	-----

PROFINET conformance class	C
----------------------------	---

PROFINET specification	V2.3
------------------------	------

Shared device/input	yes
---------------------	-----

Diagnostics

Actuator warning	per channel via LED and BUS
------------------	-----------------------------

Diagnostic	No voltage, Under voltage
------------	---------------------------

Diagnostic via BUS	per module and channel
--------------------	------------------------

Diagnostic via LED	per module and channel
--------------------	------------------------

LED display	Ethernet connection/data traffic
-------------	----------------------------------

Cable break	per port
-------------	----------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
-------------------------------------	------

Mechanical data | Mounting data

Suitable for mounting type	2-hole screw mounting
----------------------------	-----------------------

Height	37 mm
--------	-------

Width	63 mm
-------	-------

Depth	225 mm
-------	--------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
----------------------------	--------

Operating temperature max.	55 °C
----------------------------	-------

Storage temperature min.	-25 °C
--------------------------	--------

Storage temperature max.	70 °C
--------------------------	-------

Connection type 4

Connection type 1	X0-X7
-------------------	-------

Connection type 2	XD1
-------------------	-----

Connection type 3	XD2
-------------------	-----

Connection type 4	XF1, XF2
-------------------	----------

Family construction form	M12
--------------------------	-----

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Coding	A
--------	---

No. of poles	5
--------------	---

PIN 1	24 V DC (US)
-------	--------------

PIN 2	DI
-------	----

PIN 3	0 V (US)
PIN 4	DI
PIN 5	PE
Family construction form	M12
Gender	male
Color contact carrier	black
Coding	L
No. of poles	5
PIN 1	24 V DC (US)
PIN 2	0 V (UA)
PIN 3	0 V (US)
PIN 4	24 V DC (UA)
PIN 5	n.c.
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	L
No. of poles	4
PIN 1	24 V DC (US)
PIN 2	0 V (UA)
PIN 3	0 V (US)
PIN 4	24 V DC (UA)
Mounting method	inserted, screwed
Tightening torque	0,6 Nm
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	D
No. of poles	4
PIN 1	TD +
PIN 2	RD +
PIN 3	TD -
PIN 4	RD -