

## TREE 16 TX Metall 2GE 14 FE - Unmanaged Gigabit Switch - 16 Ports/

TREE 16 TX Metall 2GE 14 FE - Unmanaged Gigabit Switch - 16 ports

Art.No.: 58174 Weight: 0.715 Country of origin: TW

Model designation: TREE 16 TX Metall 2GE 14 FE


16 port unmanaged switch


Connection cables are in the online shop under "Connection Technology".

## **Link to Product**

## Illustration







Product may differ from Image







ī	е	а	α	е	r	

Material short text TREE 16 TX Metall 2GE 14 FE

## Commercial data

**URL Webshop** https://shop.murrelektronik.com/58174

GTIN 4048879762076



stay connected

ECLASS-6.0	19170106
ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-7.1	19170106
ECLASS-8.0	19170106
ECLASS-8.1	19170106
ECLASS-9.0	19170402
ECLASS-9.1	19170106
ECLASS-10.0.1	19170402
ECLASS-10.1	19170402
ECLASS-11.0	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
ECLASS-13.0	19170402
ECLASS-14.0	19170402
ETIM-5.0	EC000734
ETIM-6.0	EC000734
ETIM-7.0	EC000734
ETIM-8.0	EC000734
customs tariff number	85176200
EAN	4048879762076
Packaging unit	1
Electrical data   Supply	
Operating voltage DC min.	9 V
Operating voltage DC max.	48 V
Power consumption max.	7.4 W
	7.4 W
Industrial communication	
Data transmission rate max.	1,000 Mbit/s
Industrial communication   Ethernet fur	nctionality
VLAN unmanaged (IEEE 802.1Q)	yes
Switch type	unmanaged
duplex	Full duplex
Auto-negotiation	yes
Auto-crossover	yes
Diagnostics	
Alarm contact	no
Diagnostic	No voltage
LED display	Ethernet connection/data traffic
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP20
	IFZU
Mechanical data   Material data	
Material housing	Metal
Color housing	black
Mechanical data   Mounting data	
Height	145 mm
Width	54 mm
Depth	113 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Environmental characteristics   Climatic	c c
Operating temperature min.	0 °C

The information in this Product-PDF has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-10-31



Operating temperature max.	70 °C
Storage temperature min.	-20 °C
Storage temperature max.	70 °C
Connection type 2	
Connection type 1	16
Connection type 2	X1
Family construction form	RJ45
No. of poles	8
Gender	female
Color contact carrier	black
PIN 1	TD+
PIN 2	TD -
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -
PIN 7	n.c.
PIN 8	n.c.
Family construction form	terminal
No. of poles	5
Gender	male
Color contact carrier	green
Connection	Plug-in terminals RK
PIN 1	FE
PIN 2	0 V
PIN 3	24 V DC (UB 1)
PIN 4	0 V
PIN 5	24 V DC (UB 2)