

MAI20 I/O MODULE RELAY

4 digital inputs, 4 digital relay outputs

Art.No.: 56478

Weight: 0.125

Country of origin: SG

Model designation: MAI20 DI4/0,15A DO4R/2,0A AB

Digital inputs/relay outputs

DI4 - 0.15 A DO4R - 2 A (AB)

AB-Slave

Protection IP20


Current manuals can be downloaded at: www.murrelektronik.com

Link to Product

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ETIM-5.0	EC001599
customs tariff number	85176200
customs tariff number	85176200
GTIN	4048879705622
GTIN	4048879705622
Packaging unit	1
Packaging unit	1

Electrical data | Supply

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-05-13

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Operating voltage external DC min.	12 V
Operating voltage external DC max.	30 V
Bus voltage AS-Interface DC min.	26,5 V
Bus voltage AS-Interface DC max.	31,6 V
Current consumption AS-i port max.	230 mA
Total current max.	8 A
module supply	Via system connection or by additional feed-in

Electrical data | Input

Type input	PNP, for 3-wire sensors or mechanical switches
Input current max.	5,6 mA
Overload resistant	yes
Short-circuit protected	yes
Current carrying capacity max.	0,15 A

Electrical data | Output

Output voltage AC	250 V
Output voltage DC	30 V
Output current per pin max.	2 A

Industrial communication | Bus data

Address setting type	Addressing socket, Master
Slave address range	(0), 1 A...31 A, 1 B...31 B

Industrial communication | AS-Interface

Profile (IO.ID.ID2)	S-7.A.7
---------------------	---------

Diagnostics

Diagnostic	No voltage
Diagnostic via LED	per module
LED display	Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	125 mm
Width	19 mm
Depth	99 mm

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C

Connection type 2

Connection type 1	Asi Bus
Connection type 2	I / O
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	yellow
No. of poles	4
PIN 25	AS-i +
PIN 26	AS-i +
PIN 27	AS-i -
PIN 28	AS-i -

Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	black
No. of poles	24
PIN 1	I 1
PIN 2	I 2
PIN 3	I 3
PIN 4	I 4
PIN 5	I -
PIN 6	I -
PIN 7	I -
PIN 8	I -
PIN 9	I +
PIN 10	I +
PIN 11	I +
PIN 12	I +
PIN 15	O 13
PIN 16	O 14
PIN 17	O 23
PIN 18	O 24
PIN 19	O 33
PIN 20	O 34
PIN 21	O 43
PIN 22	O 44