

**Xelity 4TX Unmanaged Switch 4 Port 100Mbit**

Art.No.: 58810

Weight: 0.128

Country of origin: DE

Model designation: Xelity 4TX

4 port unmanaged switch

Connection cables are in the online shop under "Connection Technology".

**Link to Product****Illustration**

Product may differ from Image

**Header**

Material short text Xelity 4TX

**Commercial data**URL Webshop <https://shop.murrelektronik.com/58810>

GTIN 4048879785952

ECLASS-6.0 19170106

ECLASS-6.1 19170106

ECLASS-7.0 19170106

ECLASS-7.1 19170106

ECLASS-8.0 19170106

ECLASS-8.1 19170106

ECLASS-9.0 19170402

ECLASS-9.1 19170106

ECLASS-10.0.1 19170402

ECLASS-10.1 19170402

ECLASS-11.0 19170402

ECLASS-11.1 19170402

ECLASS-12.0 19170402

ECLASS-13.0 19170402

ECLASS-14.0 19170402

ETIM-5.0 EC000734

ETIM-6.0 EC000734

ETIM-7.0	EC000734
ETIM-8.0	EC000734
customs tariff number	85176200
EAN	4048879785952
Packaging unit	1

#### Electrical data | Supply

Operating voltage DC min.	9.5 V
Operating voltage DC max.	31.5 V
Current consumption max.	35 mA

#### Industrial communication

Data transmission rate max.	100 Mbit/s
-----------------------------	------------

#### Industrial communication | Ethernet functionality

VLAN unmanaged (IEEE 802.1Q)	yes
Switch type	unmanaged
duplex	Full duplex
Auto-negotiation	yes
Auto-crossover	yes

#### Diagnostics

Alarm contact	no
Diagnostic	No voltage
LED display	Ethernet connection/data traffic

#### Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Invers-polarity protection	yes
Over voltage protection	yes

#### Mechanical data | Material data

Material housing	Plastic
Color housing	black

#### Mechanical data | Mounting data

Height	140 mm
Width	30 mm
Depth	85.1 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

#### Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	60 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C

#### Connection type 2

Connection type 1	4
Family construction form	RJ45
No. of poles	8
Gender	female
Color contact carrier	black
PIN 1	TD +
PIN 2	TD -
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -

PIN 7	n.c.
PIN 8	n.c.
Family construction form	terminal
No. of poles	4
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	24 V DC (UB 1)
PIN 2	0 V
PIN 3	PE
PIN 4	n.c.