

Tree 8TX IP67 Metal - Unmanaged Switch - 8xM12

Art.No.: 58161
Weight: 0.49
Country of origin: DE
Model designation: TREE 8TX IP67 8xM12


8 port unmanaged switch
Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



| Commercial data | |
|-----------------------------|---------------|
| ECLASS-6.0 | 19170106 |
| ECLASS-6.1 | 19170106 |
| ECLASS-7.0 | 19170106 |
| ECLASS-8.0 | 19170106 |
| ECLASS-9.0 | 19170402 |
| ECLASS-10.1 | 19170402 |
| ECLASS-11.1 | 19170402 |
| ECLASS-12.0 | 19170402 |
| ETIM-5.0 | EC000734 |
| customs tariff number | 85176200 |
| customs tariff number | 85176200 |
| GTIN | 4048879536509 |
| GTIN | 4048879536509 |
| Packaging unit | 1 |
| Packaging unit | 1 |
| Electrical data Supply | |
| Operating voltage DC min. | 9 V |
| Operating voltage DC max. | 30 V |
| Industrial communication | |
| Data transmission rate max. | 100 MBit/s |

Industrial communication | Ethernet functionality

| | |
|------------------------------|-------------|
| Auto-crossover | yes |
| Auto-negotiation | yes |
| duplex | Full duplex |
| Switch type | unmanaged |
| VLAN unmanaged (IEEE 802.1Q) | yes |

Diagnostics

| | |
|---------------|----------------------------------|
| Alarm contact | no |
| Diagnostic | No voltage |
| LED display | Ethernet connection/data traffic |

Device protection | Electrical

| | |
|-------------------------------------|------|
| Degree of protection (EN IEC 60529) | IP67 |
|-------------------------------------|------|

Mechanical data | Material data

| | |
|------------------|------------------|
| Material housing | Zinc die-casting |
| Coating housing | Nickeled |

Mechanical data | Mounting data

| | |
|----------------------------|-----------------------|
| Suitable for mounting type | 4 hole screw mounting |
| Height | 145 mm |
| Width | 55 mm |
| Depth | 31 mm |

Environmental characteristics | Climatic

| | |
|----------------------------|--------|
| Operating temperature min. | -25 °C |
| Operating temperature max. | 60 °C |
| Storage temperature min. | -40 °C |
| Storage temperature max. | 80 °C |

Connection type 2

| | |
|--------------------------|-------------------|
| Connection type 1 | 4-7 |
| Connection type 2 | Power |
| Mounting method | inserted, screwed |
| Tightening torque | 0,6 Nm |
| Family construction form | M12 |
| Gender | female |
| Color contact carrier | black |
| Coding | D |
| No. of poles | 4 |
| PIN 1 | TD + |
| PIN 2 | RD + |
| PIN 3 | TD - |
| PIN 4 | RD - |
| Family construction form | M12 |
| Gender | male |
| Color contact carrier | black |
| Coding | A |
| No. of poles | 5 |
| PIN 1 | 24 V DC (UB 1) |
| PIN 2 | 24 V DC (UB 2) |
| PIN 3 | 0 V |
| PIN 4 | 0 V |
| PIN 5 | PE |