

E-Stop 22 2NC M12(5)

Emergency-Stop

Art.No.: 69051  
Weight: 0.039  
Country of origin: HU  
Model designation: E-Stop 22 2NC M12(5)


E-Stop 22 2NC M12(5)  
Emergency-Stop  
Mounting hole 22,3 mm  
Connection M12 (5-polig)

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.1	27371244
ECLASS-7.0	27371244
ECLASS-8.0	27371244
ECLASS-9.0	27371244
ECLASS-10.1	27371244
ECLASS-11.1	27371244
ECLASS-12.0	27371244
ETIM-5.0	EC002034
ETIM-6.0	EC002034
ETIM-7.0	EC002034
ETIM-8.0	EC002034
customs tariff number	85365011
customs tariff number	85365011
GTIN	4065909019238
GTIN	4065909019238
Packaging unit	1
Packaging unit	1

<b>Electrical data   Supply</b>	
Rated operating voltage AC-15	35 V
Rated operating voltage DC-13	35 V
<b>Electrical data   Input</b>	
Short-circuit current	1000 A
<b>Electrical data   Output</b>	
Switching power max.	0,25 W
Voltage switching AC min.	1 V
Switching voltage AC max.	35 V
Switching voltage AC max. (UL 60947)	30 V
Voltage switching DC min.	1 V
Switching voltage DC max.	35 V
Switching voltage DC max. (UL 60947)	30 V
Switching current min.	1 mA
Switching current max.	100 mA
<b>Installation   Connection</b>	
Family construction form	M12
<b>Installation   Pin assignment</b>	
Coding	A
No. of poles	5
<b>Device protection   Electrical</b>	
Installation height max. ASL	2000 m
Pollution Degree	2
Short circuit protective device (SCPD)	fuse 250 V / 0.1 A / 1.5 kA gG quick
Rated insulation voltage	250 V
Overvoltage category (EN 60950-1)	II
<b>Device protection   Mechanical</b>	
Mechanical endurance	50000 Cycles
Mechanical endurance B10	65000 Cycles
Operating life B10d	84500 Cycles
UL enclosure type rating front side	type 4X
<b>Device protection   Media</b>	
Salt-spray resistance (IEC 60068-2-11)	yes
<b>Mechanical data</b>	
Can be illuminated	no
Actuating function	latching
Color	red
Color collar	yellow
Shape collar	round
Contact type	2 Ö
<b>Mechanical data   Material data</b>	
Material housing	Plastic
Material contact	Gold
<b>Mechanical data   Mounting data</b>	
Mounting method	Threaded ring
Installation height	39,6 mm
Mounting depth	36,4 mm
Mounting hole	22,3 mm
Height	30 mm
Width	29,8 mm

Depth	69,7 mm
Grid min.	30 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-40 °C
Operating temperature max.	85 °C
Derating from	40 °C
Storage temperature min.	-40 °C
Storage temperature max.	90 °C
Relative humidity max. (operation)	93 %

**Connection type 1**

Family construction form	M12
Gender	male
Color contact carrier	black
Coding	A
No. of poles	5
PIN 1	NC 2
PIN 2	NC 1
PIN 4	NC 2
PIN 5	NC 1