

TREE 16 TX Metall 2GE 14 FE - Unmanaged Gigabit Switch - 16 Ports/

TREE 16 TX Metall 2GE 14 FE - Unmanaged Gigabit Switch - 16 ports

Art.No.: 58174



Weight: 0.715 kg

Country of origin: TW

Model designation: TREE 16 TX Metall 2GE 14 FE

16 port unmanaged switch

Connection cables are in the online shop under "Connection Technology".

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

| | |
|-----------------------|---|
| URL Webshop | https://shop.murrelektronik.com/58174 |
| GTIN | 4048879762076 |
| Customs tariff number | 85176200 |
| ECLASS-6.0 | 19170106 |

| | |
|--|----------------------------------|
| ECLASS-6.1 | 19170106 |
| ECLASS-7.0 | 19170106 |
| ECLASS-7.1 | 19170106 |
| ECLASS-8.0 | 19170106 |
| ECLASS-8.1 | 19170106 |
| ECLASS-9.0 | 19170106 |
| ECLASS-9.1 | 19170106 |
| ECLASS-10.0.1 | 19170402 |
| ECLASS-10.1 | 19170402 |
| ECLASS-11.0 | 19170402 |
| ECLASS-11.1 | 19170402 |
| ECLASS-12.0 | 19170402 |
| ECLASS-13.0 | 19170402 |
| ECLASS-14.0 | 19170402 |
| ETIM-5.0 | EC000734 |
| ETIM-6.0 | EC000734 |
| ETIM-7.0 | EC000734 |
| ETIM-8.0 | EC000734 |
| customs tariff number | 85176200 |
| EAN | 4048879762076 |
| Packaging unit | 1 |
| Electrical data Supply | |
| Operating voltage DC min. | 9 V |
| Operating voltage DC max. | 48 V |
| Power consumption max. | 7,4 W |
| Industrial Communication | |
| Data transmission rate max. | 1.000 Mbit/s |
| Industrial communication Ethernet functionality | |
| VLAN unmanaged (IEEE 802.1Q) | Yes |
| Switch type | unmanaged |
| duplex | Full duplex |
| Auto-negotiation | Yes |
| Auto-crossover | Yes |
| Diagnostics | |
| Alarm contact | No |
| Diagnostic | No voltage |
| LED display | Ethernet connection/data traffic |
| Device protection Electrical | |
| Degree of protection (EN IEC 60529) | IP20 |
| Mechanical data Material data | |
| housing | Metal |
| Color housing | black |
| Mechanical data Mounting data | |
| Height | 145 mm |
| Width | 54 mm |
| Depth | 113 mm |
| Mounting method | geschnappt |
| Suitable for mounting type | Mounting rail TH35, (EN 60715) |
| Environmental characteristics Climatic | |
| Operating temperature min. | 0 °C |
| Operating temperature max. | 70 °C |

Ambient temperature (storage, transport) -20 °C ... 70 °C

Connection type 2

| | |
|--------------------------|----------------------|
| Connection type 1 | 16 |
| Connection type 2 | X1 |
| Family construction form | RJ45 |
| No. of poles | 8 |
| Gender | female |
| Color contact carrier | black |
| PIN 1 | TD + |
| PIN 2 | TD - |
| PIN 3 | RD + |
| PIN 4 | n.c. |
| PIN 5 | n.c. |
| PIN 6 | RD - |
| PIN 7 | n.c. |
| PIN 8 | n.c. |
| Family construction form | terminal |
| No. of poles | 5 |
| Gender | male |
| Color contact carrier | green |
| Connection | Plug-in terminals RK |
| PIN 1 | FE |
| PIN 2 | 0 V |
| PIN 3 | 24 V DC (UB 1) |
| PIN 4 | 0 V |
| PIN 5 | 24 V DC (UB 2) |