

8 Port unmanaged Gigabit Switch 4 PoE Ports IP20 metal

Art.No.: 58192
Weight: 0.7
Country of origin: TW
Model designation: TREE 8TX 4PoE GE

8 Port Unmanaged IP20 PoE Gigabit Switch
24 V power supply
4 PoE ports

Link to Product

Illustration



Product may differ from Image



Commercial data

URL Webshop	https://shop.murrelektronik.com/58192
GTIN	4048879845090
ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-7.1	19170106
ECLASS-8.0	19170106
ECLASS-8.1	19170106
ECLASS-9.0	19170402
ECLASS-9.1	19170106
ECLASS-10.0.1	19170402
ECLASS-10.1	19170402
ECLASS-11.0	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
ECLASS-13.0	19170402
ECLASS-14.0	19170402
EAN	4048879845090

Electrical data | Supply

Operating voltage DC min.	12 V
Operating voltage DC max.	57 V

PoE voltage amplifier yes

Industrial communication

Data transmission rate max. 1,000 MBit/s

Industrial communication | Ethernet functionality

VLAN unmanaged (IEEE 802.1Q) no

Switch type unmanaged

duplex Full duplex

Auto-negotiation yes

Auto-crossover yes

Diagnostics

Alarm contact yes

Diagnostic No voltage

LED display Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529) IP20

Mechanical data | Material data

Material housing Metal

Color housing black

Mechanical data | Mounting data

Height 145 mm

Width 57.8 mm

Depth 113 mm

Mounting method geschnappt

Suitable for mounting type Mounting rail TH35, (EN 60715)

Environmental characteristics | Climatic

Operating temperature min. -40 °C

Operating temperature max. 70 °C

Storage temperature min. -40 °C

Storage temperature max. 85 °C

Connection type 2

Connection type 1 8

Connection type 2 X1

Family construction form RJ45

No. of poles 8

Gender female

Color contact carrier black

PIN 1 TD +

PIN 2 TD -

PIN 3 RD +

PIN 4 n.c.

PIN 5 n.c.

PIN 6 RD -

PIN 7 n.c.

PIN 8 n.c.

Family construction form terminal

No. of poles 7

Gender male

Color contact carrier green

Connection Plug-in terminals RK

PIN 1 FE

PIN 2 V 1 -

PIN 3	V 1 +
PIN 4	Relay (NO)
PIN 5	Relay (NO)
PIN 6	V 2 -
PIN 7	V 2 +