

## 8 Port unmanaged Gigabit Switch 4 PoE Ports IP20 metal

Art.No.: 58192  
 Weight: 0.700 kg  
 Country of origin: TW  
 Model designation: TREE 8TX 4PoE GE


8 Port Unmanaged IP20 PoE Gigabit Switch  
 24 V power supply  
 4 PoE ports

### Link to Product

#### Illustration



Product may differ from Image



#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/58192">https://shop.murrelektronik.com/58192</a>
GTIN	4048879845090
Customs tariff number	85176200
ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-7.1	19170106
ECLASS-8.0	19170106
ECLASS-8.1	19170106
ECLASS-9.0	19170106
ECLASS-9.1	19170106
ECLASS-10.0.1	19170402
ECLASS-10.1	19170402
ECLASS-11.0	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
ECLASS-13.0	19170402
ECLASS-14.0	19170402
customs tariff number	85176200
EAN	4048879845090
Packaging unit	1

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-05-04

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | [shop@murrinc.com](mailto:shop@murrinc.com) | [shop.murrinc.com](http://shop.murrinc.com)

<b>Electrical data   Supply</b>	
Operating voltage DC min.	12 V
Operating voltage DC max.	57 V
PoE voltage amplifier	Yes
<b>Industrial Communication</b>	
Data transmission rate max.	1.000 Mbit/s
<b>Industrial communication   Ethernet functionality</b>	
VLAN unmanaged (IEEE 802.1Q)	No
Switch type	unmanaged
duplex	Full duplex
Auto-negotiation	Yes
Auto-crossover	Yes
<b>Diagnostics</b>	
Alarm contact	Yes
Diagnostic	No voltage
LED display	Ethernet connection/data traffic
<b>Device protection   Electrical</b>	
Degree of protection (EN IEC 60529)	IP20
<b>Mechanical data   Material data</b>	
housing	Metal
Color housing	black
<b>Mechanical data   Mounting data</b>	
Height	145 mm
Width	57,8 mm
Depth	113 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-40 °C
Operating temperature max.	70 °C
Ambient temperature (storage, transport)	-40 °C ... 85 °C
<b>Connection type 2</b>	
Connection type 1	8
Connection type 2	X1
Family construction form	RJ45
No. of poles	8
Gender	female
Color contact carrier	black
PIN 1	TD +
PIN 2	TD -
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -
PIN 7	n.c.
PIN 8	n.c.
Family construction form	terminal
No. of poles	7
Gender	male
Color contact carrier	green

Connection	Plug-in terminals RK
PIN 1	FE
PIN 2	V 1 -
PIN 3	V 1 +
PIN 4	Relay (NO)
PIN 5	Relay (NO)
PIN 6	V 2 -
PIN 7	V 2 +