

**ECO-RAIL-2 POWER SUPPLY 1-PHASE,**

IN: 90 ... 132 VAC / 173 ... 264 VAC OUT: 24V/20ADC

Art.No.: 85137

Weight: 1.6

Country of origin: CN

Model designation: Eco-Rail-2 20-100-240/24

INPUT: 90...132 V AC/173...264 V AC

OUTPUT: 23...28 V DC


Current: 20 A

Mains failure bridging min.

min. 15 ms (115 V AC); min. 20 ms (230 V AC)

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

EAN

4048879694636