

8 Port unmanaged Gigabit Switch 8 PoE Ports IP20 metal

Art.No.: 58193 Weight: 0.7

Country of origin: TW

Model designation: TREE 8TX 8PoE GE 8 Port Unmanaged IP20 PoE Gigabit Switch


24 V power supply

8 PoE ports

Link to Product

Illustration





Product may differ from Image







Header	
Material short text	TREE 8TX 8PoE GE
Commercial data	
URL Webshop	https://shop.murrelektronik.com/58193
GTIN	4048879844208
ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-7.1	19170106
ECLASS-8.0	19170106
ECLASS-8.1	19170106
ECLASS-9.0	19170402
ECLASS-9.1	19170106
ECLASS-10.0.1	19170402
ECLASS-10.1	19170402
ECLASS-11.0	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
ECLASS-13.0	19170402
ECLASS-14.0	19170402
customs tariff number	85176200



stay connected

EAN	4048879844208
Packaging unit	1
Electrical data Supply	
Operating voltage DC min.	12 V
Operating voltage DC max.	57 V
PoE voltage amplifier	yes
Industrial communication	
	4.000 M 1/4
Data transmission rate max.	1,000 Mbit/s
Industrial communication Ethernet function	ionality
VLAN unmanaged (IEEE 802.1Q)	no
Switch type	unmanaged
duplex	Full duplex
Auto-negotiation	yes
Auto-crossover	yes
Diagnostics	
Alarm contact	yes
Diagnostic	No voltage
LED display	Ethernet connection/data traffic
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Material data	
Material housing	Metal
Color housing	black
·	DIQUN
Mechanical data Mounting data	
Height	145 mm
Width	57.8 mm
Depth	113 mm
Mounting method	geschnappt (TN 60745)
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	70 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C
Connection type 2	
Connection type 1	8
Connection type 2	X1
Family construction form	RJ45
No. of poles	8
Gender	female
Color contact carrier	black
PIN 1	TD+
PIN 2	TD-
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -
PIN 7	n.c.
PIN 8	n.c.
Family construction form	terminal
No. of poles	7

The information in this Product-PDF has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-11-04



Gender	male
Color contact carrier	green
Connection	Plug-in terminals RK
PIN 1	FE
PIN 2	V1-
PIN 3	V1+
PIN 4	Relay (NO)
PIN 5	Relay (NO)
PIN 6	V 2 -
PIN 7	V 2 +