

Emparro AS-Interface (AS-i) Power Supply 3-PHASE,

IN: 360 - 500VAC OUT: 30-32V/4ADC

Art.No.: 85383
Weight: 0.68
Country of origin: CZ
Model designation: Emparro 4-3x360-500/30


INPUT: 3× 324...572 V AC / 450...745 V DC
OUTPUT: 30...32 V DC
Current: 4 A

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701
ECLASS-10.1	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ETIM-5.0	EC002540
customs tariff number	85044095
customs tariff number	85044095
GTIN	4048879627627
GTIN	4048879627627
Packaging unit	1
Packaging unit	1
Electrical data	
Number of devices parallel connection max.	3
Number of devices series connection max.	3

Parallel connection	yes
Series connection	yes
Electrical data Supply	
Power frequency	50 ... 60 Hz
Electrical data Input	
Input voltage AC min.	324 V
Input voltage AC max.	572 V
Input voltage 1 AC	360 V
Input voltage 2 AC	500 V
Input voltage DC min.	450 V
Input voltage DC max.	745 V
Input current at input voltage 1 AC	0,45 A
Input current at input voltage 2 AC	0,3 A
Fuse protection primary side internal	6,3 A
Characteristic back-up fuse	Inertia
Inrush current max.	9,5 A @ 500 V
Phase number input	3
Efficiency	92,5 % @ 3× 400 V AC, 91,8 % @ 3× 480 V AC
Electrical data Output	
Output voltage DC	30,5 V
Output voltage DC min.	30 V
Output voltage DC max.	32 V
Output voltage adjustable	yes
Output current	4,8 A
Duration Power Boost min.	5 s
Mains failure bridging min.	20 ms @ 3× 360 V AC
Power Boost	150 %
Ripple effective max.	20 mV
Spikes (s-s) max.	50 mV
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Overload protection output	yes
Short-circuit protection output	yes
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Height	143 mm
Width	50 mm
Depth	143 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	70 °C
Derating from	70 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C
Relative humidity min. (operation)	5 %
Relative humidity max. (operation)	95 % no condensation
Conformity	
Product standard	IEC 61010-2-201
EMC	EN 61000-3-2
Low Voltage Directive	EN 61204-3

Approvals	
SEMI F47	compliant
Connection type 2	
Connection type 1	Input
Connection type 2	Output
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	4
PIN 1	PE
PIN 2	L 1
PIN 3	L 2
PIN 4	L 3
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	6
PIN 1	AS-i -
PIN 2	AS-i -
PIN 3	0 V
PIN 4	AS-i +
PIN 5	13
PIN 6	14