

## Xelity 8TX managed switch 8 port 1000Mbit ProfiNet IP20

Art.No.: 58825

Weight: 0.164

Country of origin: DE

Model designation: Xelity 8TX M GE PN

The Xelity product range is intended for use in industrial environments. The switches have TX ports for twisted pair cables

8-port PROFINET managed switch in IP20 plastic housing

8 RJ45 ports with Gigabit transmission speed

Power connection via push-in terminals


Connection cables are in the online shop under "Connection Technology".

### [Link to Product](#)

#### Illustration



Product may differ from Image



#### Commercial data

ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-8.0	19170106
ECLASS-9.0	19170401
ECLASS-10.1	19170401
ECLASS-11.1	19170401
ECLASS-12.0	19170401
customs tariff number	85176200
GTIN	4065909004722
Packaging unit	1

#### Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	9 V
Operating voltage DC max.	30 V
Idle current min.	112,5 mA
Idle current max.	187,5 mA
Power consumption max.	3,6 W

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-05-11

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | [shop@murrinc.com](mailto:shop@murrinc.com) | [shop.murrinc.com](http://shop.murrinc.com)

Current consumption max. 400 mA

#### Industrial communication

Supported protocol PROFINET  
Data transmission rate max. 1000 MBit/s

#### Industrial communication | Ethernet functionality

Auto-crossover yes  
Auto-negotiation yes  
duplex Full duplex  
LLDP frames forwarding  
Ring topology RSTP, STP  
Switch type managed

#### Industrial communication | Profinet

FSU (Fast-Start-Up) no  
MRP client yes  
PROFINET Netload Class III  
PROFINET addressing DCP  
PROFINET conformance class B  
PROFINET specification V2.4  
Shared device/input no

#### Industrial communication | IIoT functions

Webserver HTTPS

#### Switch Management

Addressing BOOTP/DHCP client, DCP, SSH-Befehlszeile  
NAT 1:1  
RSTP (IEEE 802.1D-2004, IEC 62439-1) Default on  
Simple Network Management Protocol (SNMP) v1 + v2c + v3 (default active)  
VLAN managed (IEEE 802.1Q) yes  
VLANs max. (IEEE 802.1Q) 64  
Time synchronization Real-time clock, NTP client

#### Diagnostics

Alarm contact no  
Diagnostic No voltage  
Remote maintenance Open VPN client  
LED display Ethernet connection/data traffic  
Port mirroring 1:1, N:1  
RMON yes  
SNMP traps yes  
Syslog yes

#### Device protection | Electrical

Degree of protection (EN IEC 60529) IP20  
Invers-polarity protection yes  
Over voltage protection yes

#### Mechanical data | Material data

Material housing Plastic  
Color housing gray

#### Mechanical data | Mounting data

Mounting method geschnappt  
Suitable for mounting type Mounting rail TH35, (EN 60715)  
Height 105 mm  
Width 41,6 mm

Depth 85,1 mm

#### Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	75 °C
Derating from	65 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C
Transport temperature min.	-40 °C
Transport temperature max.	85 °C
Relative humidity min. (operation)	5 %
Relative humidity max. (operation)	95 % no condensation

#### Connection type 2

Connection type 1	8
Family construction form	RJ45
Gender	female
Color contact carrier	black
No. of poles	8
PIN 1	DA +
PIN 2	DA -
PIN 3	DB +
PIN 4	DC +
PIN 5	DC -
PIN 6	DB -
PIN 7	DD +
PIN 8	DD -
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	4
PIN 1	24 V DC (UB 1)
PIN 2	0 V
PIN 3	PE
PIN 4	n.c.