



**TRANSFER MODULE FOR DIN RAIL MOUNTING**

Art.No.: 596154  
 Weight: 0.053  
 Country of origin: CZ  
 Model designation: MVZ-SZ Ü-Modul

23-pole  
 for 1× 11- and 1× 12-pole spring clamp terminals  
 pre-wired to push-in spring clamp terminals

[Link to Product](#)

**Illustration**



Product may differ from Image



**Commercial data**

ECLASS-6.0	27143424
ECLASS-6.1	27260708
ECLASS-7.0	27141152
ECLASS-8.0	27141152
ECLASS-9.0	27141152

The information in this Product-PDF has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-05-11

ECLASS-10.1	27141152
ECLASS-11.1	27141152
ECLASS-12.0	27141152
ETIM-5.0	EC001583
customs tariff number	85369010
customs tariff number	85369010
GTIN	4048879315692
GTIN	4048879315692
Packaging unit	1
Packaging unit	1

#### Electrical data | Supply

Operating voltage DC	24 V
Operating current max.	8 A

#### Installation

Connection cross-section solid max.	1 mm <sup>2</sup>
-------------------------------------	-------------------

#### Installation | Connection

Connection	Push-In spring clamp terminals
------------	--------------------------------

#### Device protection | Electrical

Overvoltage category (EN 60664-1)	III
-----------------------------------	-----

#### Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	75 mm
Width	45 mm
Depth	65 mm

#### Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C