

Emparro IP67 Power Supply 1-Phase

OUT: 24VDC 2x3.8A - 7/8" 4P NEC - PELV

Art.No.: 85679

Weight: 1.85

Country of origin: CZ

Model designation: Emparro67 Hybrid 3,8-100-240/24 NEC2 7/8

Emparro®67 Hybrid (PELV)

2x MICO 7/8" IOL

4-pole

Current: 2x 3.8 A galvanically separated

INPUT: 90...265 V AC/90...265 V DC

OUTPUT: 24...28 V DC

Preventive Diagnostic

Over current protection device


controllable via IO-Link

Link to Product

Illustration



Product may differ from Image



Header

Material short text Emparro67 Hybrid 3,8-100-240/24 NEC2 7/8

Commercial data

URL Webshop	https://shop.murrelektronik.com/85679
GTIN	4048879797771
ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-7.1	27049002
ECLASS-8.0	27049002
ECLASS-8.1	27049002
ECLASS-9.0	27040701
ECLASS-9.1	27040701

ECLASS-10.0.1	27040701
ECLASS-10.1	27040701
ECLASS-11.0	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ECLASS-13.0	27040701
ECLASS-14.0	27040701
ETIM-5.0	EC002540
ETIM-6.0	EC002540
ETIM-7.0	EC002540
ETIM-8.0	EC002540
customs tariff number	85044095
EAN	4048879797771
Packaging unit	1

Electrical data

Security level	SELV
Parallel connection	no
Series connection	no

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Input voltage AC	240 V
Input voltage AC min.	90 V
Input voltage AC max.	265 V
Input voltage DC min.	90 V
Input voltage DC max.	265 V
Current input AC	1.2 A
Inrush current max.	59 A @ 230 V
Power factor	230 V AC
Efficiency	91.8 % @ 115 V AC 92.9 % @ 230 V AC
Characteristic back-up fuse	Inertia
Fuse protection primary side internal	63 A

Electrical data | Output

Output voltage adjustable	yes
Output voltage DC	24 V
Output voltage DC min.	24 V
Output voltage DC max.	28 V
Number of output channels	2
Output current per channel max.	3.8 A
Mains failure bridging min.	20 ms @ 230 V AC
Spikes (s-s) max.	150 mV
Ripple effective max.	10 mV

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Overload protection output	yes
Short-circuit protection output	yes
Overtemperature protection output	yes

Mechanical data | Mounting data

Height	216 mm
Width	110 mm
Depth	53 mm
Suitable for mounting type	6 hole screw mounting

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	80 °C
Derating from	55 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C
Relative humidity min. (operation)	4 %
Relative humidity max. (operation)	100 %

Technical Data | Reliability

MTBF	0 h EN IEC 61709, SN 29500, EN ISO 13849-1
Additional condition MTTF, MTBF	40 °C

Conformity

Product standard	IEC 61010-2-201
EMC	EN 55022 B, EN 61000-3-2
Low Voltage Directive	EN 61204-3

Connection type 2

Connection type 1	Output
Connection type 2	Signal
Family construction form	7/8"
No. of poles	4
Gender	female
Color contact carrier	black
PIN 1	24 V DC (Out 2)
PIN 2	24 V DC (Out 1)
PIN 3	0 V PE
PIN 4	0 V PE
Family construction form	M12
No. of poles	4
Coding	A
Gender	male
Color contact carrier	black
PIN 1	L + (24 V DC) (In)
PIN 2	DI / DO (I / Q)
PIN 3	L - (0 V)
PIN 4	IO-Link (C / Q)