

## Emparro Power Supply 3-PHASE

IN: 360 - 500VAC OUT: 24-28V/20ADC

Art.No.: 85692

Weight: 1.256 kg

Country of origin: CZ

Model designation: Emparro 20-3x360-500/24

INPUT: 3× 324...572 V AC / 450...745 V DC

OUTPUT: 24...28 V DC


Current: 20 A

### Link to Product

#### Illustration



Product may differ from Image



#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/85692">https://shop.murrelektronik.com/85692</a>
GTIN	4048879538633
Customs tariff number	85044095
ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-7.1	27049002
ECLASS-8.0	27049002
ECLASS-8.1	27049002
ECLASS-9.0	27040701
ECLASS-9.1	27040701
ECLASS-10.0.1	27040701
ECLASS-10.1	27040701
ECLASS-11.0	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ECLASS-13.0	27040701
ECLASS-14.0	27040701
ETIM-5.0	EC002540

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-04-23

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | [shop@murrinc.com](mailto:shop@murrinc.com) | [shop.murrinc.com](http://shop.murrinc.com)

ETIM-6.0	EC002540
ETIM-7.0	EC002540
ETIM-8.0	EC002540
customs tariff number	85044095
EAN	4048879538633
Packaging unit	1

**Electrical data**

Parallel connection	Yes
Number of devices parallel connection max.	3
Series connection	Yes
Number of devices series connection max.	3

**Electrical data | Supply**

Protective measure	SELV
Power frequency	50 ... 60 Hz

**Electrical data | Input**

Phase number input	3
Input voltage AC min.	324 V
Input voltage AC max.	572 V
Nominal input voltage AC	3 × 360 V ... 500 V
Input voltage DC min.	450 V
Input voltage DC max.	745 V
Nominal current AC	3 × 1.3 A @ 360 V, 1 A @ 500 V
Inrush current max.	13 A @ 500 V
Power factor	3× 500 V AC
Efficiency	94.8 % @ 3× 400 V AC 94.5 % @ 3× 480 V AC
Characteristic back-up fuse	Inertia
Fuse protection primary side internal	6,3 A

**Electrical data | Output**

Output voltage adjustable	Yes
Output voltage DC	24 V
Output voltage DC min.	24 V
Output voltage DC max.	28 V
Output current	24 A
Mains failure bridging min.	40 ms @ 3× 500 V AC
Power Boost	150 %
Duration Power Boost min.	5 s
Spikes (s-s) max.	90 mV
Ripple effective max.	20 mV

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP20
Overload protection output	Yes
Short-circuit protection output	Yes

**Mechanical data | Mounting data**

Height	143 mm
Width	65 mm
Depth	167 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

**Environmental characteristics | Electromagnetic compatibility**

Interference emission	EN IEC 55011, IEC 61000-3-2
-----------------------	-----------------------------

**Environmental characteristics | Climatic**

Operating temperature min.	-40 °C
Operating temperature max.	70 °C
Derating	45 °C
Ambient temperature (storage, transport)	-40 °C ... 85 °C
Relative humidity (operation)	5 % ... 95 %
Additional condition relative humidity	no condensation

### Conformity

Product standard	EN IEC 61010-2-201, EN 61204-3
------------------	--------------------------------

### Approvals

SEMI F47	compliant
----------	-----------

### Connection type 3

Connection type 1	Alarm
Connection type 2	Input
Connection type 3	Input / Output
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	13
PIN 2	14
Family construction form	terminal
No. of poles	4
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	PE
PIN 2	L 1
PIN 3	L 2
PIN 4	L 3
Family construction form	terminal
No. of poles	4
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	-
PIN 2	-
PIN 3	+
PIN 4	+