

MIRO 6,2-1OUTPUT-REL.24VDC-1S-FK(5P)**MIRO 6.2 24VDC-1S OUTPUT RELAY**

Art.No.: 6652006

Weight: 0.02

Country of origin: CZ

Model designation: MIRO 6,2-1AUSG.REL.24VDC-1S-FK(5P)

1 NO contact



6 A

24 V DC


with solder terminal

Spring clamp terminals

safe separation (EN 60947-1)

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0

27371001

ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-8.0	27371601
ECLASS-9.0	27371601
ECLASS-10.1	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ETIM-5.0	EC001437
customs tariff number	85364900
customs tariff number	85364900
GTIN	4048879022200
GTIN	4048879022200
Packaging unit	1
Packaging unit	1

Electrical data | Input

Input voltage DC	24 V
Input voltage DC min.	19,2 V
Input voltage DC max.	30 V
Input current	14 mA

Electrical data | Output

Utilization category AC-12 (EN IEC 60947-5-1)	6 A @ 24, 6 A @ 110 V, 6 A @ 230 V
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V, 3 A @ 110 V, 3 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1 A @ 24 V, 0,2 A @ 110 V, 0,1 A @ 230 V
Switching frequency max.	10 Hz
Power rating AC max.	1500 VA
Power rating DC max.	120 W
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current DC	100 mA
Switching current max.	6 A

Diagnostics

Status indication LED	green
-----------------------	-------

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Rated surge voltage	4 kV
Electrical lifetime	20000000 Cycles

Device protection | Mechanical

Mechanical endurance	20000000 Cycles
----------------------	-----------------

Mechanical data

Drop-out time max.	15 ms
Response time max.	10 ms
Bounce time max.	1,5 ms

Mechanical data | Material data

Material contact	Ag Sn O2
------------------	----------

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	91 mm
Width	6,2 mm

Depth 70 mm

Environmental characteristics | Climatic

Operating temperature min. -25 °C
Operating temperature max. 60 °C

Connection type 5

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 13

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 NC

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 14

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 + A 1

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier black

No. of poles 1

PIN 1 - A 2