

**MODLINK MSDD DATA INSERT**

1xSUB-D9 fem./soldering + 1xSUB-D15 fem./soldering

Art.No.: 4000-68000-0310000

Weight: 0.035

Country of origin: DE

Model designation: FR.MODUL 9 pol. Bu + 15 pol. Bu

SUB-D9; SUB-D15

1× SUB-D9 (solder connection/female)

1× SUB-D15 (solder connection/female)

**Link to Product****Illustration**

Product may differ from Image

**Commercial data**

URL Webshop	<a href="https://shop.murrelektronik.com/4000-68000-0310000">https://shop.murrelektronik.com/4000-68000-0310000</a>
GTIN	4048879038027
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625

ETIM-7.0	EC002625
ETIM-8.0	EC002625
EAN	4048879038027

#### Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	40 mm

#### Environmental characteristics | Climatic

Storage temperature min.	-30 °C
Storage temperature max.	60 °C

#### SUB-D9

Family construction form	SUB-D9
Gender	female
No. of poles	9
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D9
Gender Rear	Solder connection
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	3 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42.4 V
Current operating max. (UL)	175 mA

#### SUB-D15

Family construction form	SUB-D15
Gender	female
No. of poles	15
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D15
Gender Rear	Solder connection
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42.4 V
Current operating max. (UL)	175 mA