

**MODLINK MSDD DBL COMBI INSERT USA 2XNEMA 5-15**

GFCI+1xRJ45 fem./fem.+1xSUB-D9 fem./male+1x3A fuse

Art.No.: 4000-68000-4130000

Weight: 0.264 kg

Country of origin: CN

Model designation: Fr.Modul-AB-125-15-GFCI-SC+RJ45+DB9F/M+f


2x NEMA-GFCI 5-15 (screw terminals)

1x RJ45, 8-pole metal, CAT5e (female/female)

1x SUB-D9 (male/female)

1x fuse (3 A)

with touch protection

**Link to Product****Illustration**

Product may differ from Image

**Commercial data**

URL Webshop	<a href="https://shop.murrelektronik.com/4000-68000-4130000">https://shop.murrelektronik.com/4000-68000-4130000</a>
GTIN	4048879369282
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806

ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
EAN	4048879369282
Packaging unit	1

**Mechanical data | Mounting data**

Height	88 mm
Width	116 mm
Depth	72 mm

**Environmental characteristics | Climatic**

Ambient temperature (storage, transport)	-40 °C ... 70 °C
--	------------------

**Fuse**

Operating voltage AC	250 V
Operating voltage DC	32 V
Nominal current	3 A
Protector type	OC - Overcurrent type
UL Use group	A
Terminals (UL 1077)	0
Tripping current (UL 1077)	1
Overload rating (UL 1077)	1
Short-circuit current rating (UL 1077)	1.0 KA, U1
UL CCN	QVNU2
UL-Standard	UL 1077
CSA Class	3215-30
CSA-Standard	CSA C22.2 No. 144.1-16

**USA**

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	Yes
Connection cross section max.	6 mm <sup>2</sup>
AWG number max.	10
Operating voltage AC	125 V
Operating current	15 A
UL CCN	KCXS, KCXS7
UL-Standard	UL 943
CSA-Standard	CSA C22.2 No. 144.1-16

**SUB-D9**

Family construction form	SUB-D9
Gender	female
No. of poles	9
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D9
Gender Rear	male
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	3 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA

RJ45	
Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA