

**MODLINK MSDD DBL COMBI INSERT USA 2XNEMA 5-15**

GFCI+1x3A fuse

Art.No.: 4000-68000-4140000

Weight: 0.245


Country of origin: CN

Model designation: Fr.Modul-AB-125-15-GFCI-SC+fuse3A

2× NEMA-GFCI 5-15 (screw terminals)

1× fuse (3 A)

with touch protection

**[Link to Product](#)****Illustration**

Product may differ from Image

**Header**

Material short text Fr.Modul-AB-125-15-GFCI-SC+fuse3A

**Commercial data**

URL Webshop	<a href="https://shop.murrelektronik.com/4000-68000-4140000">https://shop.murrelektronik.com/4000-68000-4140000</a>
GTIN	4048879369299
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806

ECLASS-14.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
EAN	4048879369299
Packaging unit	1

#### Mechanical data | Mounting data

Height	88 mm
Width	116 mm
Depth	72 mm

#### Environmental characteristics | Climatic

Storage temperature min.	-40 °C
Storage temperature max.	70 °C

#### Fuse

Operating voltage AC	250 V
Operating voltage DC	32 V
Nominal current	3 A

#### USA

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	yes
Connection cross section max.	6 mm <sup>2</sup>
AWG number max.	10
Operating voltage AC	125 V
Operating current	15 A