


**MODLINK MSDD DBL COMBI INSERT USA 2XNEMA 5-15**

GFCI+1xRJ45 fem./fem.+1xSUB-D9 fem./fem.+1x3A fuse

2× NEMA-GFCI 5-15 (screw terminals)  
 1× RJ45, 8-pole metal, CAT5e (female/female)  
 1× SUB-D9 (female/female)  
 1× fuse (3 A)  
 with touch protection

**Link to Product****Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879462846
Packaging unit	1

**Mechanical data | Mounting data**

Height	88 mm
Width	116 mm
Depth	72 mm

**Environmental characteristics | Climatic**

Storage temperature min.	-40 °C
Storage temperature max.	70 °C

<b>Fuse</b>	
Operating voltage AC	250 V
Operating voltage DC	32 V
Nominal current	3 A
<b>USA</b>	
Connection cross section max.	6 mm <sup>2</sup>
AWG number max.	10
Operating voltage AC	125 V
Operating current	15 A
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes
<b>SUB-D9</b>	
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Operating current	3 A
Current operating max. (UL)	175 mA
Family construction form	SUB-D9
Family type Back side	SUB-D9
Gender	female
Gender Rear	female
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
No. of poles	9
<b>RJ45</b>	
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e
Looking techniques	Snap-in connector