

## MODLINK MSDD FRAME DBL METALIC

Closure 3 mm double bit incl. pluggable knob

Art.No.: 4000-68523-0000001

Weight: 0.155

Country of origin: DE


Model designation: Rahmenmodul 2-fach metallic 3mm Doppelb.

Frame: plastic PA black Lid: plastic, ABS metallic Closure: 3 mm double bit with attachable rotation knob

## **Link to Product**

## Illustration





Product may differ from Image

0

0

0

0

0

0

0

0

0

0

0

0

0

0



Material short text	Rahmenmodul 2-fach metallic 3mm Doppelb.
Header	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
0	
U	

Commercial data



URL Webshop	https://shop.murrelektronik.com/4000-68523-0000001
GTIN	4048879368865
ECLASS-6.0	27189217
ECLASS-6.1	27189260
ECLASS-7.0	27189260
ECLASS-7.1	27189260
ECLASS-8.0	27189260
ECLASS-8.1	27189260
ECLASS-9.0	27182810
ECLASS-9.1	27189260
ECLASS-10.0.1	27182810
ECLASS-10.1	27182810
ECLASS-11.0	27182810
ECLASS-11.1	27182810
ECLASS-12.0	27182810
ECLASS-13.0	27182810
ECLASS-14.0	27182810
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85389099
EAN	4048879368865
Packaging unit	1
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP65
Mechanical data   Material data	
Material housing	PA
Color housing	black
Material lid	ABS
Color cover	metallic
Mechanical data   Mounting data	
Height	127 mm
Width	131 mm
Depth	43 mm
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Environmental characteristics   Climatic	
	-30 °C
Operating temperature min.  Operating temperature max.	70 °C
Ambient temperature (storage, transport)	-30 °C
	-50 C
Frame	
Material housing	PA
Color housing	black
Material lid	ABS
Color cover	metallic
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-30 °C
Operating temperature max.	70 °C
Storage temperature min.	-30 °C