

Modlink MSDD-set: Frame 4000-68523-0000001,

insert 4000-68000-4120000

Art.No.: 4000-68523-4120001

Weight: 0.541 kg Country of origin: US


Model designation: MSDD_2metallic_GFCI 15A+2xRJ45+3A fuse_

with touch protection

Link to Product

Illustration







Product may differ from Image

Header	
Material short text	MSDD_2metallic_GFCl 15A+2xRJ45+3A fuse_
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68523-4120001
GTIN	4048879477970
ECLASS-6.0	27144001
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217



stay connected

ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.0	27189217
ECLASS-9.1 ECLASS-10.0.1	27182806
ECLASS-10.0.1	27182806
ECLASS-10.1 ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-11.1 ECLASS-12.0	
ECLASS-13.0	27182806 27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
customs tariff number EAN	85366990
	4048879477970
Packaging unit	1
Mechanical data Mounting data	
Height	88 mm
Width	116 mm
Depth	72 mm
Frame	
Material housing	PA
Color housing	black
Material lid	ABS
Color cover	metallic
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-30 °C
Operating temperature max.	70 °C
Storage temperature min.	-30 °C
Fuse	
Operating voltage AC	250 V
Operating voltage DC	32 V
Nominal current	3 A
USA	
Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	Yes
Connection cross section max.	6 mm ²
AWG number max.	10
Operating voltage AC	125 V
Operating current	15 A
RJ45	
Family construction form	RJ45
Family construction form Looking techniques	RJ45 Snap-in connector
Looking techniques	Snap-in connector
Looking techniques Cable category min.	Snap-in connector Cat5e



Current operating max. (UL)

175 mA