

**MSDD pass-through USB 3.0 form A, 0.6 m cable, design silver**

Art.No.: 4000-73000-0150000




Weight: 0.059


Country of origin: CZ

Model designation: MSDD PT22-S USB3.0 A/A F/M\_0.6


Pass-through

1 × USB 3.0 (female/male/0.6 m cable) form A

**[Link to Product](#)****Illustration**



Product may differ from Image



Commercial data	
URL Webshop	<a href="https://shop.murrelektronik.com/4000-73000-0150000">https://shop.murrelektronik.com/4000-73000-0150000</a>
GTIN	4048879432894
ECLASS-6.0	27143423
ECLASS-6.1	27143419
ECLASS-7.0	27440515
ECLASS-7.1	27440515
ECLASS-8.0	27440515
ECLASS-8.1	27440515
ECLASS-9.0	27440515
ECLASS-9.1	27440515
ECLASS-10.0.1	27440515
ECLASS-10.1	27440515
ECLASS-11.0	27440515
ECLASS-11.1	27440515
ECLASS-12.0	27440515
ECLASS-13.0	27440515
ECLASS-14.0	27440515
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
EAN	4048879432894
Electrical data   Supply	
Operating voltage AC	5 V
Operating voltage DC	5 V
Industrial communication	
Data transmission rate max.	5,000 MBit/s
USB specification	3.0
Device protection	
Shielded	yes
Device protection   Electrical	

Degree of protection (EN IEC 60529)	IP20, IP65
Protection NEMA	12, 3R, 4x, 4, 13, 2
Additional condition protection degree	in closed state, inserted
<b>Device protection   Mechanical</b>	
Mechanical endurance	1,500 Cycles
<b>Mechanical data   Mounting data</b>	
Depth	30 mm
Diameter	29.5 mm
Mounting depth	70 mm
Diameter cutout	22.5 mm
<b>Approvals</b>	
UL 50E	yes