

**MSDD pass-through USB 3.0 form A, 0.6 m cable, design silver**

Art.No.: 4000-73000-0150000




Weight: 0.059


Country of origin: CZ

Model designation: MSDD PT22-S USB3.0 A/A F/M\_0.6


Pass-through

1 × USB 3.0 (female/male/0.6 m cable) form A

[Link to Product](#)**Illustration**



Product may differ from Image



Header

Material short text MSDD PT22-S USB3.0 A/A F/M\_0.6

Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/4000-73000-0150000">https://shop.murrelektronik.com/4000-73000-0150000</a>
GTIN	4048879432894
ECLASS-6.0	27143423
ECLASS-6.1	27143419
ECLASS-7.0	27440515
ECLASS-7.1	27440515
ECLASS-8.0	27440515
ECLASS-8.1	27440515
ECLASS-9.0	27440515
ECLASS-9.1	27440515
ECLASS-10.0.1	27440515
ECLASS-10.1	27440515
ECLASS-11.0	27440515
ECLASS-11.1	27440515
ECLASS-12.0	27440515
ECLASS-13.0	27440515
ECLASS-14.0	27440515
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85444290
EAN	4048879432894
Packaging unit	1

Electrical data | Supply

Operating voltage AC	5 V
Operating voltage DC	5 V
Operating current max.	900 mA

Industrial communication

Data transmission rate max.	5,000 Mbit/s
-----------------------------	--------------

USB specification	3.0
-------------------	-----

**Device protection**

Shielded	yes
----------	-----

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP20, IP65
-------------------------------------	------------

Protection NEMA	12, 3R, 4x, 4, 13, 2
-----------------	----------------------

Additional condition protection degree	in closed state, inserted
--	---------------------------

**Device protection | Mechanical**

Mechanical endurance	1,500 cycles
----------------------	--------------

**Mechanical data | Mounting data**

Depth	30 mm
-------	-------

Diameter	295 mm
----------	--------

Mounting depth	70 mm
----------------	-------

Diameter cutout	225 mm
-----------------	--------

**Approvals**

UL 50E	yes
--------	-----